



Raccordi Pead Stampati
Moulded HDPE Fittings



PEAFIT

Raccords en PEHD Injectés
Junciones en PEAD Inyectadas


GOMITO 90° CODOLO LUNGO

Elbow 90° Extended

Coude 90° Long

Codo 90° Mango Largo

Gruppo: C01



				Art. 7411	Art. 7416		Art. 7425		
				PE 100					
				SDR17 - PN10 - S8 MOP3 *		SDR11 - PN16 - S5 MOP5 *		SDR7,4 - PN25 - S3,2 MOP9 *	
d	Z	L	Box	s	Weight Kg	s	Weight Kg	s	Weight Kg
20	Art. 7911- 7916 Curva 90° - Bend 90°								
25									
32									
40									
50									
63	111	65		3,8		5,8	0,16	8,6	
75	128	75		4,5	0,34	6,8	0,38	10,3	
90	130	80		5,4	0,51	8,2	0,52	12,3	
110	149	88		6,6	0,80	10,0	0,62	15,1	
125	165	92		7,4	1,16	11,4	1,63	17,1	
140	183	100		8,3	1,34	12,7	2,29	19,2	
160	191	110		9,5	2,18	14,6	3,32	21,9	
180	225	120		10,7	2,38	16,4	3,82	24,6	
200	219	117		11,9	2,94	18,2	4,48	27,4	
225	238	121		13,4	4,00	20,5	5,86	30,8	
250	304	175		14,8	6,54	22,7	9,44	34,2	
280	340	197		15,6	9,30	25,4	12,86	38,3	
315	370	210		18,7	12,22	28,6	18,10	43,1	

MOP: Massima Pressione Operativa Gas
Pression Maximum Operative en Bar pour Gaz


Maximum Operative Pressure in Bar for Gas
Maxima Presion Operativa en Bar para Gas

TEE 90° CODOLO LUNGO

Tee 90° Extended

Tee 90° Long

Tee 90° Mango Lungo

Gruppo: C01


					Art. 8011		Art. 8016		Art. 8025	
					PE 100					
					SDR17 - PN10 - S8 MOP3 *		SDR11 - PN16 - S5 MOP5 *		SDR7,4 - PN25 - S3,2 - MOP9 *	
d	Z	L	l	Box	s	Weight Kg	s	Weight Kg	s	Weight Kg
20	107	35,5	54,5				3,0	0,03	3,0	
25	117	40	59				3,0	0,04	3,5	
32	144	45	71				3,0	0,07	4,5	
40	168	51	84				3,7	0,12	5,5	
50	189	57	95				4,6	0,21	6,9	
63	225	65	99	10	3,8	0,28	5,8	0,36	8,6	
75	260	75	115	5	4,5	0,38	6,8	0,54	10,3	
90	286	80	127,5	4	5,4	0,80	8,2	0,86	12,3	
110	315	88	145,5	1	6,6	1,12	10,0	1,40	15,1	
125	357	92	157	1	7,4	1,49	11,4	2,03	17,1	
140	370	100	172,5	1	8,3	2,35	12,7	2,91	19,2	
160	470	110	192,5	1	9,5	3,26	14,6	4,54	21,9	
180	521	133,5	257	1	10,7	5,24	16,4	6,93	24,6	
200	490	114	245	1	11,9	6,16	18,2	7,98	27,4	
225	548	146	270	1	13,4	8,16	20,5	10,95	30,8	
250	622	148	310	1	14,8	11,56	22,7	15,06	34,2	
280	694	160	347	1	15,6	15,58	25,4	20,86	38,3	
315	752	170	375	1	18,7	21,14	28,6	28,46	43,1	
355	874	190	437	1	21,1	32,20	32,2	43,20	48,50	
400	940	200	470	1	23,7	40,96	36,3	56,46	54,70	

 MOP: Massima Pressione Operativa Gas
 Pression Maximum Operative en Bar pour Gaz


 Maximum Operative Pressure in Bar for Gas
 Maxima Presion Operativa en Bar para Gas

CALOTTA CODOLO LUNGO

Cap Extended

Bouchon Long

Tapa Mango Largo

Gruppo: C01


				Art. 8111		Art. 8116		Art. 8125	
				PE 100					
				SDR17 - PN10 - S8 MOP3 *		SDR11 - PN16 - S5 MOP5 *		SDR7,4 - PN25 - S3,2 - MOP9 *	
d	Z	L	Box	s	Weight Kg	s	Weight Kg	s	Weight Kg
20	45	40				3,0	0,01	3,0	
25	48	40				3,0	0,01	3,5	
32	54	45				3,0	0,02	4,5	
40	61	50				3,7	0,03	5,5	
50	71	57	50			4,6	0,05	6,9	
63	79	65	60			5,8	0,09	8,6	
75	79	75	40	4,5	0,92	6,8	0,16	10,3	
90	93	80	24	5,4	0,15	8,2	0,26	12,3	
110	105	88	12	6,6	0,26	10,0	0,44	15,1	
125	124	92	6	7,4	0,37	11,4	0,61	17,1	
140	140	100	5	8,3	0,52	12,7	0,86	19,2	
160	144	110	8	9,5	0,75	14,6	1,18	21,9	
180	178,5	141,5	1	10,7	1,14	16,4	1,70	24,6	
200	181,5	127	1	11,9	1,40	18,2	2,06	27,4	
225	211,5	141,5	1	13,4	1,97	20,5	2,96	30,8	
250	230	152	1	14,8	2,64	22,7	3,94	34,2	
280	257	162	1	15,6	3,68	25,4	5,36	38,3	
315	262	167	1	18,7	4,93	28,6	7,10	43,1	

 MOP: Massima Pressione Operativa Gas
 Pression Maximum Operative en Bar pour Gaz


 Maximum Operative Pressure in Bar for Gas
 Maxima Presion Operativa en Bar para Gas

RIDUZIONE CODOLO LUNGO

Reduced Extended

Reduction Long

Reduccion Mango Largo

Gruppo: C01


						Art. 7211			Art. 7216					
						PE 100								
						SDR17 - PN10 - S8 MOP3 *			SDR11 - PN16 - S5 MOP5 *					
d	d1	Z	L	L1	Box	s	s1	Weight Kg	s	s1	Weight Kg			
25	20	87							2,3	1,9	0,02			
32	20	92							3	1,9	0,02			
	25	92							2,3	0,02				
40	20	102							3,7	1,9	0,03			
	25	102								2,3	0,04			
	32	102								3	0,04			
50	25	118							4,6	2,3	0,06			
	32	118								3	0,06			
	40	126								3,7	0,07			
63	20	129	65	42	50							5,8	2	0,09
	32	131		50	54								3	0,96
	40	137		55	48								3,7	0,11
	50	143		60	38								4,6	0,12
75	40	148	75	55	24				4,5			6,8	3,7	0,15
	50	151		60	25	3,0	0,13							
	63	159		65	20	3,8	0,17							
90	50	160	80	60	15	5,4			8,2	4,6	0,24			
	63	159		65	15					3,8	0,21			
	75	174		75	12					4,5	0,22			

 MOP: Massima Pressione Operativa Gas
 Pression Maximum Operative en Bar pour Gaz

 Maximum Operative Pressure In Bar for Gas
 Maxima Presion Operativa en Bar para Gas